

車いす適合表

WHEELCHAIR

車いすはオプションや設定、製造時期によって様々な仕様があります。
そのため車いすの仕様によっては、この表に記載の情報と異なる場合がございます。詳しくは取扱店へお問い合わせください。

アクセルレシーバーの

BRAND	MODE
-------	------

Ø(直径)	長さ
10	10
12	12
15	15
20	20
25	25
30	30
35	35
40	40
45	45
50	50
55	55
60	60
65	65
70	70
75	75
80	80
85	85
90	90
95	95
100	100
105	105
110	110
115	115
120	120
125	125
130	130
135	135
140	140
145	145
150	150
155	155
160	160
165	165
170	170
175	175
180	180
185	185
190	190
195	195
200	200
205	205
210	210
215	215
220	220
225	225
230	230
235	235
240	240
245	245
250	250
255	255
260	260
265	265
270	270
275	275
280	280
285	285
290	290
295	295
300	300
305	305
310	310
315	315
320	320
325	325
330	330
335	335
340	340
345	345
350	350
355	355
360	360
365	365
370	370
375	375
380	380
385	385
390	390
395	395
400	400
405	405
410	410
415	415
420	420
425	425
430	430
435	435
440	440
445	445
450	450
455	455
460	460
465	465
470	470
475	475
480	480
485	485
490	490
495	495
500	500
505	505
510	510
515	515
520	520
525	525
530	530
535	535
540	540
545	545
550	550
555	555
560	560
565	565
570	570
575	575
580	580
585	585
590	590
595	595
600	600
605	605
610	610
615	615
620	620
625	625
630	630
635	635
640	640
645	645
650	650
655	655
660	660
665	665
670	670
675	675
680	680
685	685
690	690
695	695
700	700
705	705
710	710
715	715
720	720
725	725
730	730
735	735
740	740
745	745
750	750
755	755
760	760
765	765
770	770
775	775
780	780
785	785
790	790
795	795
800	800
805	805
810	810
815	815
820	820

Aria	2.0 AI	12.7	51
Aria	Ultra	12.7	51
Aria	Speciale	12.7	51
Aria	The 1.0	12.7	51
Aria	Pilux	12.7	51
Bischoff & Bischoff	Pyro Start	12	51
Bischoff & Bischoff	Pyro Start Plus	12	51
Bischoff & Bischoff	Pyro Start Plus SL	12	51
Bischoff & Bischoff	Exon XXL		
Bischoff & Bischoff	S-Eco 2		
Bischoff & Bischoff	S-Eco 300		
Bischoff & Bischoff	S-Eco 300 XL		
Dietz	Tauron		
Invacare	Action 2 NG	12	54
Invacare	Action 3 NG	12	54
Invacare	Action 3 RC	12	54
Invacare	Action 4 NG	12	54
Invacare	Action 5	12	54
KARMA MEDICAL	S-ERGO	12.7	51
Küschall	Ultra light	12.7	51
Küschall	K-Series	12.7	51
Küschall	KSL	12.7	51
Küschall	Champion	12.7	51
Küschall	Compact	12.7	51
Meyra	Eurochair camber 0 ° & 1°	12	51
Meyra	Eurochair camber 2° & 3°	12	62
Meyra	Eurochair 2 camber 0 ° & 1°	12	51
Meyra	Eurochair 2 camber 2° & 3°	12	62
Meyra	FEMTO R	12	51
Meyra	FEMTO X/S camber 0 ° & 1°	12	51
Meyra	FEMTO X/S camber 2° & 3°	12	62
Meyra	NANO	12	51
Meyra	NANO X camber 0°& 1°	12	51
Meyra	NANO X camber 2°& 3°	12	62
Meyra	NANO C	12	51
Meyra	NANO S camber 0°& 1°	12	51
Meyra	NANO S camber 2°& 3°	12	62
Meyra	SMART F/S camber 0° & 1°	12	51
Meyra	SMART F/S camber 2° & 3°	12	62
Meyra	AVANTI PRO	12	64
Meyra	AVANTI	12	64
Meyra	HURRICANE	12	51
Motion Composite	Move	12.7	54
Motion Composite	Helio A6	12.7	54
Motion Composite	Helio A7	12.7	54
Motion Composite	Helio C2	12.7	54
Motion Composite	Veloce	12.7	54
Motion Composite	APEX Alu	12.7	54
Motion Composite	APEX C	12.7	54

ブレーキレバー付ホイール Skeed(スキード)



QR Axle

Adapter RTS

[illegible]

ブレーキシステム付ホイール Dreeft (ドリーフ)



QR Axle

Adapter RTD

[illegible]

スペシャルアダプタ
(Skeed、Dreeft共通)

**オプション・警告事
その他の情報**

適応及び画像

Adapter A

Adapter C

Adapter B

Not compatible	Not compatible	alidated and recommende	30	NC carbon bar option	2.0 / Ultra
Not compatible	Not compatible	alidated and recommende	30	NC carbon bar option	2.0 / Ultra
Not compatible	Not compatible	Not compatible	/		
Not compatible	Not compatible	Not compatible	/		
Not compatible	Not compatible	Not compatible			
Validated	Validated	Not compatible	/	Drum brake	Action 2
Validated	Validated	Not compatible	/	Drum brake, Rocking chair	Action 3
Validated	Not compatible	Not compatible	/	incompatible for rocking chair	
Validated	Not compatible	Validated	25,2	Drum brake, position of axis barrel	Action 4
Validated	Validated	Not compatible	/	Drum brake	Action 5
Not compatible	Not compatible	Validated	25,2	B compact + Corne plate	
Validated	Validated	Validated	22	Brake on hub, Drum brake	Ultra Light
Not compatible	Not compatible	Validated with condition	30	Brake in wheels, camber 0° and 3°, Vario axis	K-series
Not compatible	Not compatible	Validated with condition	30	Lenght camber bar	KSL
Validated	Validated	Validated	22	Anti-tip wheel : compatible ad	Champion
Validated	Validated	Validated	22	Drum brake	Compact
Validated	Not compatible	Validated	25,2	Drum brake	Eurochair
Validated	Not compatible	Validated	25,2	Adaptor A : Only compatible with upper hole	Eurochair 2
					Nano
					Nano X
					Nano X
					Nano C
					Smart F/S
					Avanti Pro
					Avanti
Validated	Not compatible	Not compatible		B compact + corne plate	
Validated	Not compatible	Not compatible		B peanut + compact bolt	MOVE
Validated	Not compatible	Not compatible		B compact + corne plate	
Validated	Not compatible	Not compatible		B peanut + compact bolt	Helio A6
Validated	Not compatible	Not compatible		Requires a nut on the outside	Helio A7
Validated	Not compatible	Not compatible		Requires a nut on the outside	Helio C2
Not compatible	Not compatible	Validated	28	Adapter B not compatible with camber	
Not compatible	Not compatible	Validated	28	Adapter B not compatible with camber	Apex Alu

Mouvly / Janton	Trace S	12.7	41	[12,7 x 136] DRE-6-41-136-K	Validated  WITH FRAME PROTECTOR 	[12,7 x 136] DRE-6-41-136-K	Validated and recommended	Not compatible	Not compatible	Not compatible	/	SKEED :Only with Eppur Axle 12,7 x 136 + 32mm spacer + plastic trap for the rear position DREEFT : 136mm axle + 17,5 spacer	Trace S
Offcarr  variable de	Heka												
Offcarr  variable de	Themis			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	QLR8			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	QUASAR			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	QUASAR GT			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	QPX	12	41	[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture	Not compatible	Not compatible	Not compatible			
Offcarr  variable de	FIXED			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	EOS			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture	Not compatible	Not compatible	Not compatible	/		
Offcarr  variable de	EOS 3			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture					 WARNING : The axle receiver depths are not stable	
Offcarr  variable de	VENUS			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	VENUS ELITE			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	VENUS ADVENTURE			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	FENICE			[12,7 x 107] PAR-2-41-107-K	Validated with condition	[12,7 x 116] DRE-X-85-113-K	Validated with condition						
Offcarr  variable de	IDRA 2.0			[12,7 x 107] PAR-2-41-107-K	Validated with condition	[12,7 x 116] DRE-X-85-113-K	Validated with condition						
Offcarr  variable de	IDRA 2.E			[12,7 x 107] PAR-2-41-107-K	Validated with condition	[12,7 x 116] DRE-X-85-113-K	Validated with condition						
Offcarr  variable de	ALHENA			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	DIVA			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	HALLEY			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	HEKO			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Offcarr  variable de	VEGA			[12,7 x 107] PAR-2-41-107-K	Validated on picture	[12,7 x 116] DRE-X-85-113-K	Validated on picture						
Ortinea	Freelance				Validated on picture		Validated on picture						
Ottobock	Motus CS	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Motus CS
Ottobock	Motus CV	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Motus CV
Ottobock	Motus Hemi	12	54	[12 x 117] PAR-2-40-117-H-K	Validated with condition	[12 x 123] DRE-6-40-123-H-K	Validated with condition	Validated	Validated	Not compatible	/	Drum brake	Motus Hemi
Ottobock	Motus XXL	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Motus XXL
Ottobock	Avantgarde CS	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Avantgarde CS
Ottobock	Avantgarde 4	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Avantgarde 4
Ottobock	Avantgarde 4 DS	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Avantgarde 4 DS
Ottobock	Avantgarde 4 DV	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible	/	Drum brake	Avantgarde 4 DV
Ottobock	Avantgarde CLT	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Not compatible		Drum brake	Avantgarde 4 DV
Ottobock	Ventus	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Not compatible	Validated	25.2		Ventus
Ottobock	Zenit aluminium	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Not compatible	Validated	30		Zenit
Ottobock	Zenit	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Not compatible	Validated	30		Zenit
Ottobock	Zenit R	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Not compatible	Validated	30		Zenit R
Panthera	X2 (carbon)	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated  WITH FRAME PROTECTOR 	[12,7 x 116] DRE-X-85-113-K	Validated  WITH FRAME PROTECTOR 	Not compatible	Not compatible	Not compatible			
Panthera	X3 (carbon)	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated  WITH FRAME PROTECTOR 	[12,7 x 116] DRE-X-85-113-K	Validated  WITH FRAME PROTECTOR 	Not compatible	Not compatible	Validated with condition	30	Setup of the axle receiver	
Panthera	S3	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated with condition	30		
Panthera	U3	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	30		Photos
Proactiv  variable	Speedy 4all Ergo	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy 4you Ergo	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy 4all	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy F2	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy F4	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy A1	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy A2	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Proactiv	Speedy 4 Teen	12	62	[12 x 130] PAR-2-40-130-H-K	Validated with condition	[12 x 135] DRE-6-40-135-H-K	Validated with condition					Adaptor RTS / RTD : Check the distance frame / axle receiver	
Proactiv	Lift Activ	12	62	[12 x 130] PAR-2-40-130-H-K	Validated on picture	[12 x 135] DRE-6-40-135-H-K	Validated on picture	Not compatible	Not compatible	Not compatible			
Proactiv	Lift Solid	12	62	[12 x 130] PAR-2-40-130-H-K	Validated on picture	[12 x 135] DRE-6-40-135-H-K	Validated on picture						
Proactiv	Traveler	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended	Validated					
Proactiv	Traveler 4all Ergo	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended	Not compatible	Not compatible	Not compatible			
Proactiv	Traveler 4you Ergo	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended						
Progeo	Joker	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Not compatible	Not compatible	Validated	22		
Progeo	Joker Carbone	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Not compatible	Not compatible	Validated	22	B-Compact on barrel end + corner plate	Joker carbone
Progeo	Joker energy	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	alidated and recommend	22	B-compact on barrel end B-compact on barrel end	Photos
Progeo	Joker R2	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Not compatible	Not compatible	Validated	22	Axe-receiver tube : 25mm Ave-receiver end : 22mm (B compact)	Photos
Progeo	Ego Custom	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated and recommend	Not compatible	Validated	22	Barrel diameter for B compact	Photos
Progeo	Ego Carbon	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Validated and recommend	Not compatible	Validated	22		Photos
Progeo	Ego	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Validated	Not compatible	Validated	22	Barrel diameter for B compact	Photos
Progeo	Basic Light	12	62	[12 x 130] PAR-2-40-130-H-K	Validated and recommended	[12 x 135] DRE-6-40-135-H-K	Validated and recommended		Not compatible				

Progeo	Carbomax	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated and recommended	[12,7 x 99] DRE-X-85-99-K	Validated and recommended	Not compatible	Not compatible	Not compatible	22	WARNING : risk of collision of the stop bracket B compact with 22	Photos
Progeo	Duke	12.7	32	[12,7 x 96] PAR-2-41-96-K	Validated Δ WITH FRAME PROTECTOR Δ	[12,7 x 99] DRE-X-85-99-K	Validated Δ WITH FRAME PROTECTOR Δ	Not compatible	Not compatible	Validated	22	WARNING CARBONE	
Progeo	Exelle	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated and recommend	Validated	Validated	22	OPTION : contact Eppur	Photos
Progeo	Exelle Junior	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated and recommend	Validated	Validated	22	Number of spacers depends on the wheel?	Exelle
Progeo	Exelle Vario	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated and recommend	Validated	Validated	22	B-compact + corne plate B-Classique + corne plate	Exelle Junior
Progeo	Noir 2.0	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated Δ WITH FRAME PROTECTOR Δ	[12,7 x 123] DRE-6-41-123-K	Validated Δ WITH FRAME PROTECTOR Δ	Not compatible	Not compatible	Validated	22	WARNIG : supports on carbon to be validated by Progeo. Only in Bcompact version	Exelle vario
Progeo	Tekna Advance	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated on picture	[12,7 x 123] DRE-6-41-123-K	Validated on picture	Validated and recommend	Validated		22	Check axis length on support	Noir 2.0
Progeo	Yoga	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated on picture	[12,7 x 123] DRE-6-41-123-K	Validated on picture	Validated and recommend	Validated	Validated	22	B-Ultra compact	Yoga
Progeo	Tekna Tilt 2.0	12.7	32	[12,7 x 96] PAR-2-41-96-K	NC $\rightarrow$ See special adaptor	[12,7 x 99] DRE-X-85-99-K	NC $\rightarrow$ See special adaptor	Not compatible	Validated	Validated	22		Tekna Tilt
RGK	TIGA Fixed	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended	Not compatible	Not compatible	Validated with condition	32		
RGK	TIGA Adjustable	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended						
RGK	TIGA SUB 4 Fixed	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended			Validated with condition	32		
RGK	TIGA SUB 4 Adjustable	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended			Validated with condition	32		
RGK	Octane Fixed (standard)	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended			Validated with condition	32		
RGK	Octane Adjustable	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended						
RGK	Octane SUB4 Fixed	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended	Not compatible	Not compatible	Validated with condition	32		
RGK	Octane SUB4 Adjustable	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended						
RGK	HILITE	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended						
RGK	MAXLITE	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated and recommended	[12,7 x 136] DRE-6-41-136-K	Validated and recommended						
Rupiani	Sixi	12	51	[12 x 117] PAR-2-40-117-H-K	Validated on picture	[12 x 123] DRE-6-40-123-H-K	Validated on picture	Validated	Validated	Validated			Sixi
Sunrise BREZZY	Style x ultra	12	56	[12 x 117] PAR-2-40-117-H-K	Validated and recommended	[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Style x Ultra
Sunrise BREZZY	Helix2	12.7	69		Validated and recommended		Validated and recommended						
Sunrise Quickie	Easy 200	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Easy 200
Sunrise Quickie	Easy 300	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Easy 300
Sunrise Quickie	Easy Max	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Easy Max
Sunrise Quickie	Life	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Life
Sunrise Quickie	Life R	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Life R
Sunrise Quickie	Life T	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	25,2	Drum brake	Life T
Sunrise Quickie	Helium	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	28		Helium
Sunrise Quickie	Argon²	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	28		Argon²
Sunrise Quickie	Xenon² SA	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	22	Drum brake	Xenon² SA
Sunrise Quickie	Xenon²	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	22	Drum brake/Warning wheelcha	Xenon²
Sunrise Quickie	Xenon² Hybrid	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	22	Drum brake	Xenon² Hybrid
Sunrise Quickie	Néon²	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Sunrise Quickie	Krypton R	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated Δ WITH FRAME PROTECTOR Δ	[12,7 x 123] DRE-6-41-123-K	Validated Δ WITH FRAME PROTECTOR Δ			Validated	22		
Sunrise Quickie	Krypton F	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	22		Krypton F
Sunrise Quickie	Nitrum (ex-helium)	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	30		Nitrum
Sunrise Quickie	Nitrum Pro	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Sunrise Quickie	Nitrum Hybrid	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Sunrise Quickie	QSS X	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated	Validated	Validated	28		QSSX
Sunrise Quickie	Life T	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Validated and recommend	Validated	Validated	25,2	Same frame plate as QSSX but # axle receiver	
Schmicking	X-Design	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Schmicking	X-Design Ultra Light	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Schmicking	L-Design	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Schmicking	F-Design	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated on picture	[12,7 x 123] DRE-6-41-123-K	Validated on picture						
Schmicking	Fully	12.7	51	[12,7 x 117] PAR-2-41-117-K		[12,7 x 123] DRE-6-41-123-K							
Schmicking	Duschrollstuhl	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated on picture	[12,7 x 123] DRE-6-41-123-K	Validated on picture						
Tilite	ZRA	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended			Validated	32		
Tilite	ZR	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended			Validated on picture	32		
Tilite	TR	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	32		
Tilite	TRA	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
Tilite	Aero Z	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
TNS	Activator 2.5	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended					Screw flight is M16 and removable	Photos
TNS	Activator	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended						
TNS	RSX	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended						
TNS	Proval	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended						
TNS	Activator FC	12.7	45	[12,7 x 107] PAR-2-41-107-K	Validated and recommended	[12,7 x 116] DRE-X-85-113-K	Validated and recommended						
TRACKZ	HPPIus - rigid	12.7	57		NC $\rightarrow$ See special adaptor		NC $\rightarrow$ See special adaptor					Compatibility kit available, with a separate price offer	
TRACKZ	HPPIus - with suspension	12.7	54	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						
TRACKZ	TJ Plus - rigid	12.7	57		NC $\rightarrow$ See special adaptor		NC $\rightarrow$ See special adaptor					Compatibility kit available, with a separate price offer	
TRACKZ	TJ Plus - with suspension	12.7	54	[12,7 x 117] PAR-2-41-117-K	Validated and recommended	[12,7 x 123] DRE-6-41-123-K	Validated and recommended						

TRACKZ	HP4 - rigid	12.7	57		NC → See special adaptor		NC → See special adaptor					Compatibility kit available, with a separate price offer	
TRACKZ	HP4 - with suspension	12.7	54	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
TRACKZ	HP KidZ - rigid	12.7	57		Validated with condition			Validated with condition					
Tween	Ryder élite	12.7	67	[12,7 x 129] PAR-X-85-129-K	Validated with condition		[12,7 x 136] DRE-6-41-136-K	Validated with condition		Validated	30		
Vasilli	HILO MPRO	12	54	[12 x 117] PAR-2-40-117-H-K	Validated on picture		[12 x 123] DRE-6-40-123-H-K	Validated on picture					
Ki mobility	Ethos	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Rogue 2	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended	Not compatible	Not compatible	Validated	25.2	Rogue 2
Ki mobility	Rogue ALX	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Catalyst 5	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Catalyst 5 TI	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Catalyst 5 Vx	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Rogue XP	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Ki mobility	Little wave click	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Vermeiren	V500	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V500
Vermeiren	V500 30°	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V500 30°
Vermeiren	V500 Light	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V500 light
Vermeiren	V500 Light 30°	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V500 light 30°
Vermeiren	V500 XR	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V500 XR
Vermeiren	V300	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V300
Vermeiren	V300 30°	12	54	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Validated	Validated	22	V300 30°
Vermeiren	Trigo S	12	66	[12 x 130] PAR-2-40-130-H-K	Validated and recommended		[12 x 135] DRE-6-40-135-H-K	Validated and recommended	Not compatible	Validated	Validated	25,2	Trigo S
Vermeiren	Trigo T	12	66	[12 x 130] PAR-2-40-130-H-K	Validated and recommended		[12 x 135] DRE-6-40-135-H-K	Validated and recommended	Not compatible	Validated	Validated	25,2	Before 2024 : 12x123mm After : 12x136mm Trigo T
Vermeiren	Sagitta	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Not compatible	Validated	22	Sagitta
Vermeiren	D200				Validated and recommended			Validated and recommended	Not compatible	Not compatible	Not compatible		
Vermeiren	D200 30°								Not compatible	Not compatible	Not compatible		
Wolturnus	W5	12.7	51	[12,7 x 117] PAR-2-41-117-K	Validated and recommended		[12,7 x 123] DRE-6-41-123-K	Validated and recommended					
Forta	Giro	12	51	[12 x 117] PAR-2-40-117-H-K	Validated and recommended		[12 x 123] DRE-6-40-123-H-K	Validated and recommended	Not compatible	Not compatible	Not compatible	/	